

HITPOINT

TEL:8862-26013311 FAX:8862-26013898

NO.4 Lane 505, Zhongzheng Rd,. Linkou Shiang, Taipei, Taiwan 24445 . R.O.C

Piezo Siren PS-733PDRQ

(ROHS)

DATE:2018.01.12


1. Electrical Characteristics


VER .:0

Resonant Frequency (KHz)	2.5 ~ 4.5	
Operating Voltage (Vdc)	5 ~ 15	
Rated Voltage (Vdc)	12	
Current Consumption (mA/max.)	200 at Rated Voltage	
Sound Pressure Level (dB/min.)	85 at 300cm at Rated Voltage	
Tone/Pulse Rate (Hz)	Sweep	
Operating Temperature (°C)	-20 ~ +70	
Storage Temperature (°C)	-30 ~ +80	

2. Dimensions and Material

2-1 Shape





Unit: mm



HITPOINT

TEL:8862-26013311 FAX:8862-26013898

NO.4 Lane 505, Zhongzheng Rd,. Linkou Shiang, Taipei, Taiwan 24445. R.O.C



2-2 Material

Housing	PC (Color: Red)
Lead Pin	Tin Plated Brass
Weight (Gram)	19


3. TESTING METHOD

· Standard Measurement conditions

Temperature:25 \pm 2 C Humidity:45-60%

· Acoustic Characteristics

The oscillation frequency, current consumption and sound pressure are measured by the measuring instruments shown below.



HITPOINT

TEL:8862-26013311 FAX:8862-26013898

NO.4 Lane 505, Zhongzheng Rd,. Linkou Shiang, Taipei, Taiwan 24445 . R.O.C

4. RELIABILITY

ITEMS	METHOD OF TEST AND MEASUREMENTS	PERFORMANCE
Coldness	After 98 hours of being exposed to -30 ${\mathcal C}$	No abnormality
withstanding	environment, should be returned to normal	shall exist
	environment for 2 hours, then re-proceed to test.	
Hotness	After 98 hours of being exposed to +80 $^\circ\!\! C$	No abnormality
withstanding	environment, should be returned to normal	shall exist
	environment for 2 hours, then re-proceed to test.	
Humidity	After 98 hours of being exposed to 40 $^{\circ}\!$	No abnormality
withstanding	environment in actual operation, should be	shall exist
	returned to normal environment for 2 hours, then	
	re-proceed to test.	
Durability	10sec on/10sec off ; 1000hours(180000 cycles)	No abnormality
		shall exist
Vibration	Linear vibrate frequency rate: 5~55Hz	No abnormality
withstanding	Time:180sec , applied in X, Y and Z directions for	shall exist
	3 times each.	

5. PACKAGE METHOD

<1> 84pcs per box, Total 10 boxes per carton, total 840pcs carton; Volume: L*W*H=520*335*290mm

<2 >N . W . : ; 16 KGS ; G . W . : 18 KGS ;

< 3 > RoHS Mark: